

## Chemical-resistant gloves with a unique multi-layer design, for broader protection

- **Maximized protection:** AlphaTec® 53-001 safety gloves' MICROCHEM™ multi-layer nitrile and neoprene protective barrier ensures EN 374 Type A chemical defenses and protection from acids and hydrocarbons
- **Enhanced grip:** ANSELL GRIP™ coating offers secure grip for wet or oily components
- **Elevated comfort:** AlphaTec® 53-001 chemical gloves' soft nylon inner liner grants them a comfortable feel
- **Considered aesthetics:** Their black cuff design makes them perfect for dirt-prone outdoor applications
- **Certified skin-friendly and harm-free:** Oeko-Tex® certification ensures they contain no substances harmful to human health
- **Improved durability:** AlphaTec® 53-001 industrial gloves' multi-layer coating is also abrasion-resistant, achieving EN and ANSI level 3 abrasion resistance

### Industries

- Automotive
- Oil and gas
- Chemical
- Infrastructure Maintenance
- Construction
- Automotive Aftermarket
- Emergency Medical Services
- Machinery and Equipment
- Metal fabrication

### Applications

- Chemical Handling
- Charging and blending raw materials
- Equipment maintenance and repair
- Opening and draining pumps valves or lines



### Key Features

- **MICROCHEM™ multi-layer barrier:** Acid, chemical, hydrocarbon defenses
- **ANSELL GRIP™ treatment:** Secure handling of wet or oily components
- **Soft nylon inner liner:** Safety gloves with guaranteed all-day comfort

### Technologies



### Performance Standards

ANSI/ISEA 105-2024



EN388: 2016



3121A

EN 407



XIXXXX

EN ISO 374-1:2016  
Type A



ACFGJKLMNOPST

EN ISO 374-5:2016



### Specifications

BRAND   STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 53-001	<b>Liner Material:</b> Nylon <b>Coating Material:</b> Neoprene and Nitrile <b>Featured Technology:</b> ANSELL GRIP™	6, 7, 8, 9, 10, 11	350 / 13.8	Black	<ul style="list-style-type: none"> <li>• 6 pairs in a bag; 12 bags in a carton</li> </ul>

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.