



BANDSAWS

NEW ARMORGLIDE TECHNOLOGY



LOW FRICTION



RUST RESISTANT



MAINTENANCE FREE



DURABLE COATING



ENHANCED VISIBILITY

MODEL NUMBER	PM1500T	PM1800BT	PM1800B-3T	PM2013BT	PM2013B-3T	PM2415BT	PM2415B-3T
Stock Number	PM1-1791500T	PM1-1791800BT	PM1-1791801BT	PM1-1791257BT	PM1-1791258BT	PM1-1791259BT	PM1-1791260BT
Cutting Capacity Width (Throat) (In.)	14½	18	18	20	20	24	24
Cutting Capacity Height (In.)	14	18	18	18	18	15	15
Table Type	ArmorGlide	ArmorGlide	ArmorGlide	ArmorGlide	ArmorGlide	ArmorGlide	ArmorGlide
Motor Power (HP)	3	5	5	5	5	5	5
Motor Phase (PH)	1	1	3	1	3	1	3
Motor Voltage (V.)	230	230	230/460*	230	230/460*	230	230/460*
Prewired Voltage (V.)	230	230	230	230	230	230	230
Blade Length (In.)	153	160	160	170	170	183	183
Table Height from Floor (In.)	40	38	38	36	36	35	35
Dust Port Outside Diameter (In.)	4	4	4	4	4	4	4

*PLEASE CONTACT CUSTOMER SERVICE AT 1-800-274-6848 WITH ANY REQUESTS FOR 460V MACHINES



LEARN MORE BY SCANNING QR CODE OR VISITING WOOD.POWERMATIC.COM/ARMORGLIDE