DEWALT®

TOOL CONNECT+™




# OUR MOST POWERFUL

## 20V MAX* METAL CUTTING CIRCULAR SAW†

## DCS383
## 20V MAX* XR® 7¼ IN. METAL CUTTING CIRCULAR SAW

Take on tough applications with our most powerful 20V MAX* metal cutting circular saw†. This 20V MAX* XR® 7¼ in. Metal Cutting Circular Saw delivers up to 1,400 MWO of power to help maximize productivity on the job. This tool features TOOL CONNECT+™ capabilities for next-level visibility to utilization, asset management, tool location, and safety. With a lightweight design and integrated chip collector, this circular saw is part of our best performing line of 20V MAX* power tools.

20V MAX* BRUSHLESS™

XR®

PERFORMANCE REDEFINED™

*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.
†MWO using DCBP520 battery.

GUARANTEED TOUGH.®

ICDCS383SS

# 20V MAX* XR® 7¼ IN. METAL CUTTING CIRCULAR SAW

3 YEAR LIMITED WARRANTY • Garantía limitada de 3 AÑOS • Garantie limitée de 3 ANS




**ELECTRONIC BRAKE**
Stops the blade in less than 1 second after the on/off trigger is released




*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.
†MWO using DCBP520 battery.

## SPECIFICATIONS

| | |
|---|---|
| RPM | 3,900 RPM |
| VOLTAGE | 20V MAX* |
| ARBOR SIZE | 5/8 in. |
| BLADE SIZE | 7-1/4 in. |
| MWO | 1,400† |
| TOOL WEIGHT (TOOL ONLY) | 10.7 lbs. |

## RELATED PRODUCTS (SOLD SEPARATELY)

**DWAM71440**
7-1/4 in. Metal Blade 40T



**DWAM71448**
7-1/4 in. Metal Blade 48T



**DWAM71460**
7-1/4 in. Metal Blade 60T



## PRODUCT OFFERINGS



**DCS383B**

(1) DCS383 20V MAX* XR® 7¼ in. Metal Cutting Circular Saw,
(1) DWAM71448 7-1/4 in. 48T Metal Cutting Circular Saw Blade,
(1) Blade Change Wrench



**DCS383H1**

(1) DCS383 20V MAX* XR® 7¼ in. Metal Cutting Circular Saw,
(1) DCBP520 20V MAX* XR POWERSTACK™ 5Ah Battery,
(1) DWAM71448 7-1/4 in. 48T Metal Cutting Circular Saw Blade,
(1) Blade Change Wrench, (1) DCB1106 Charger




** Regarding batteries, based on longer life (charge cycles) and more power, not in application vs. DEWALT 20V MAX* batteries with comparable amp hours.

Copyright © 2025 DEWALT. The following are trademarks for one or more DEWALT power tools, accessories, outdoor tools and equipment, anchors, and concrete adhesives: DEWALT", GUARANTEED TOUGH®, and the yellow and black color scheme."; the "D -shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

ICDCS383SS

**GUARANTEED TOUGH®** **1-800-4-DEWALT** **www.DEWALT.com**