DEWALT

OUR FASTEST CUTTING 20V MAX* RECIPROCATING SAW***



DCS384
20V MAX* XR® BRUSHLESS RECIPROCATING SAW

Take on demanding demolition and cutting applications with the 20V MAX* XR® Brushless Cordless Reciprocating Saw, our fastest cutting 20V MAX* Reciprocating Saw that delivers more power†. Featuring a 1-1/8 in. stroke length, this saw helps maximize jobsite efficiency with up to 102 cuts per charge in 2X12 pine††. Engineered for ease-of-use, this versatile saw is designed with a variable speed trigger that offers 3,000 max SPM (no-load) and a pivoting shoe to help optimize performance on tough jobs.**

20V MAX* BRUSHLESS XR®

DCS384SS

* Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.
** Cutting 2x12 Pine vs. DEWALT 20V MAX* Full-Size Reciprocating Saws using DW4802 blade and DCB2108 battery (sold separately).
† MWO, using DCB2108 (sold separately) vs. DCB205 (sold separately).
†† Cutting 2x12 Pine using DW4802 blade and DCB2108 battery (sold separately).

20V MAX* XR® BRUSHLESS RECIPROCATING SAW





POWERFUL PERFORMANCE- A brushless motor for more power†



HIGH EFFICIENCY - Up to 102 cuts per charge††

* Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.
** Cutting 2x12 Pine vs. DEWALT 20V MAX* Full-Size Reciprocating Saws using DW4802 blade and DCB2108 battery (sold separately).
† MWO, using DCB2108 (sold separately) vs. DCB205 (sold separately).
†† Cutting 2x12 Pine using DW4802 blade and DCB2108 battery (sold separately).

SPECIFICATION

KEYLESS BLADE CLAMP	Yes
STROKE/MIN (NO LOAD)	0-3,000 SPM
STROKE LENGTH	1-1/8 in.
ELECTRIC BRAKE	Yes
TOOL LENGTH	17.6 in.
TOOL WEIGHT (TOOL ONLY)	7.7 lbs

PRODUCT OFFERINGS

DCS384B

- (1) DCS384 Reciprocating Saw
- (1) Wood Cutting Reciprocating Saw Blade



DCS384WW1

- (1) DCS384 Reciprocating Saw
- (1) DCB2108 XR POWERPACK™ 8 Ah Battery
- (1) Wood Cutting Reciprocating Saw Blade
- (1) 20V MAX* Charger



WARRANTY

TOOL WARRANTY

- 3 YEAR — LIMITED WARRANTY
- 1 YEAR — FREE SERVICE
- 90 DAY — MONEY BACK GUARANTEE

BATTERY WARRANTY

- 3 YEAR — LIMITED WARRANTY
- 3 YEAR — FREE SERVICE

RELATED PRODUCTS

DWA4894

Bi-Metal Reciprocating Saw Blade Kit (8 Pc.)



Copyright ©2025 DEWALT. The following are trademarks for one or more DEWALT power tools, accessories, anchors and concrete adhesives: The yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

1-800-4-DEWALT
WWW.DEWALT.COM