



Cut



Medium Duty

Medium-duty, abrasion- and cut-resistant gloves designed for dry to slightly oily surfaces

- **Enhanced durability:** EDGE[®] 48-711 safety gloves are ideal for mediumweight applications in dry to slightly oily environments that require cut and abrasion resistance, and are more economical compared to mediumweight leather, thick cotton or aramid work gloves
- **Augmented dexterity:** These PU-coated gloves feature a seamless liner that ensures ease of movement, enabling flexibility and precise handling for delicate tasks throughout the workday
- **Increased protection:** Thanks to their elastic knitwrist, EDGE[®] 48-711 high-quality work gloves provide a snug fit that prevents dirt and debris from entering, affording better safety and hygiene for the hand as well as wrist



Industries

- Machinery and Equipment
- Maintenance
- Metal fabrication

Applications

- Assembling metal parts and components
- Handling sharp or irregular metal pieces
- Assembly of white goods
- Assembly & inspection of components
- General maintenance
- Finishing works

Key Features

- **Palm PU coating:** For protective gloves with added grip and durability
- **Seamless design:** For flexible, hard-wearing high-dexterity work gloves
- **Elastic knitwrist:** Form-fitting and comfortable hand protection gloves

Performance Standards & Regulatory Compliance

REACH Compliant



EN388: 2016



4X42B



ANSI
5
ABR



ANSI
A2
CUT

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 48-711	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Polyester, Spandex, HPPE Cuff Style: Knitwrist	13	5, 6, 7, 8, 9, 10, 11	220-280 mm; 8.66-11.02 inches	Grey	<ul style="list-style-type: none"> • 12 pairs/bag; 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell[®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.