

PIG® Grippy® Adhesive-Backed Absorbent Mat

MAT3200 Self-Sticking Absorbent Mat,(10) 16" x 24" mat pads



Stays put no matter what™! Sticks and stays down where other absorbent mats shift or slide around; perfect for workstations or around machinery in industrial facilities.

- Adhesive-backed absorbent mat stays exactly where you put it with no shifting, bunching up or flipping over to prevent slips, trips and falls in workstations and around machinery
- Proprietary adhesive sticks to the floor with a super-tight grip, but peels up easily for quick changeouts; reduces cleanup time to make your facility more productive
- Sticks to most commercial floor surfaces including concrete, vinyl, linoleum, ceramic tile, quarry tile and laminate flooring
- Tough, spunbond top layer with heavy-duty zigzag stitching stands up to foot and light-wheeled traffic; keep mat in service until it's saturated or shows signs of wear
- Multiple layers of fine-fiber polypropylene safely absorb leaks, drips and overspray of oils, coolants, solvents and water
- Traps oil, grease and grime to keep them from being tracked around; ideal for oily areas near machines and equipment
- 16" x 24" mat pads are great for catching drips and lining workbenches, countertops and toolboxes
- Leakproof backing prevents absorbed liquid from soaking through to the floor
- Dark color hides grime so the mat looks cleaner longer
- Tested and Certified by the National Floor Safety Institute (NFSI): when used as part of your floor safety program, high-traction surfaces such as PIG Grippy Absorbent Mat have been proven to reduce slip-and-fall claims by as much as 90%
- Mats take on the properties of absorbed liquids
 - always take proper precautions when handling saturated absorbents



Specifications

Style	Self-Sticking Absorbent Mat
Dimensions	16" W x 24" L
Mat Weight	Mediumweight
Recycled Content	25% or more Recycled Content
Absorbency	Up to 1 gal. per box
Absorbency per	Up to 12.8 oz. per pad
Color	Blue
Backing Material	Adhesive-Backed
Brand	PIG
Category	Grippy® Absorbent Mat
Flammability Specifications	Flame Resistant - Will melt and self-extinguish
Fluid Absorbed	Oils; Coolants; Solvents; Water; Universal
Incinerable	Yes
Industry	Industrial Facilities; Shops & Garages; Automotive; Manufacturing
Indoor/Outdoor	Indoor Use
Pad Quantity	(10) 16" x 24" mat pads
Perforated	No
Storage Temp Range	Store between 32°F and 120°F
Temperature Limit	Surface temps from 55°F to 120°F
Traffic	Light Foot Traffic
UV Resistant	No
Walking Surface	Absorbent Top
Distributor Part Number	30pz35;4983017;04088x10158
Sold as	10 pads per box
Weight	3.86 lbs.
# per Pallet	128
Composition	Absorbent - Polypropylene Stitching - Polyester Adhesive Backing - Proprietary Adhesive Material
UNSPSC	47131901
Pigalog® Page Number	Page 23

Metric Equivalent

Absorbency	Up to 3.8 L per box
Absorbency per	Up to 378.5 mL per pad
Dimensions	40.6cm W x 61cm L
Weight	1.8 kg

Technical Information

Certifications, Approvals and Ratings

NFSI Certified,ANSI B101.1- 2009,ANSI/ESD STM11.11,MIL-STD-3010C

Technical Documents

[PIG Grippy® Absorbent Mat](#)

[New Pig Adhesive-Backed Mat Notice](#)

[How to use PIG Grippy Absorbent Mat](#)

[Static Coefficient Of Friction \(SCOF\) Testing](#)

[PIG® Grippy® Absorbent Mats](#)

[29 CFR 1910.22\(a\)\(2\)](#)



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com