

PIG® Rip-&-Fit® Oil-Only Absorbent Mat Roll in Dispenser Box

MAT442 Heavyweight, 15" x 60', 1 roll



Absorb leaks and drips of oil in tight spaces and create custom mat sizes with our extra-perforated mat roll in a dispenser box. Just "rip" it along the easy-tear perfs and "fit" it into place.

- No job is too big for our heavyweight rolls; our most popular mat weight is ideal for absorbing drips of only oil and oil-based liquids on shelves and ledges and in tight or awkward spaces that require custom mat sizes; dispenser box is easy to store
- Extra perforations let you easily "rip" this PIG Mat and "fit" it to your spill without cutting; use only what you need and waste less
- Select a size that's custom to your application; create long, narrow strips to fit into small spaces
- Perforated every 3.75" across width and every 10" across length
- Absorbs and retains oil and oil-based liquids; skims oil on top of water
- Bright white color makes absorbed oil easier to see; draws attention to leaks and clearly shows saturation level
- PIG Mat lasts 2x longer than competitive mats and won't rip, tear or fray even when saturated; liquids absorb quickly for faster, easier cleanups and safer workplaces
- Can be wrung out and incinerated after use to reduce waste or for fuels blending
- Mats take on the properties of absorbed liquids
 - always take proper precautions when handling saturated absorbents



Specifications

Dimensions	15" W x 60' L
Mat Weight	Heavyweight
Absorbency	Up to 7.9 gal. per box
Absorbency per	Up to 7.9 gal. per roll
Brand	PIG
Category	Rip-&-Fit® Oil-Only Absorbent Mat

Color	White
Core Diameter	1.5"
Floating	Yes
Flammability Specifications	Flame Resistant - Will melt and self-extinguish
Fluid Absorbed	Oils; Fuels; Oil-Based Liquids (Not Water)
Incinerable	Yes
Indoor/Outdoor	Indoor Use; Short-Term Outdoor Use
Perforated	Yes
Perforated Pattern	3.75" x 10" sections
Reusable	No
Static-Dissipative	No
Traffic	Not Recommended for Foot Traffic
UV Resistant	No
Wringable	Yes
Distributor Part Number	30RA19;2422460;04088x31545
Sold as	1 roll per box
Weight	7 lbs.
# per Pallet	54
Composition	Polypropylene
UNSPSC	47131901
Pigalog® Page Number	Page 44

Metric Equivalent

Absorbency	Up to 29.9 L per box
Absorbency per	Up to 29.9 L per roll
Dimensions	38.1cm W x 18m L
Weight	3.2 kg

Technical Information

Technical Documents

PIG® Oil-Only Absorbents

29 CFR 1910.22(a)(2)

40 CFR 112.7

40 CFR 122.26

