


PIG® Oil-Only Absorbent Mat Roll

MAT458 Mediumweight, 30" x 150', 1 roll per bag

Lasts 2x longer than ordinary mats for fewer change-outs, while only absorbing oil and fuels, NOT water. Loves oil. Hates water.

- Our most cost-effective mat when you only need to absorb oil-based liquids
- Multiple layers of 100% polypropylene are thermally bonded to make PIG Mat the strongest mat on the market; won't rip, tear or fray even when saturated
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind oil or fiber residue
- Absorbs oil and fuels, NOT water
- White color tells you it's only for oils and fuels; draws attention to machine leaks and clearly shows saturation level during spill response
- Floats to clean up spills on water
- Can be wrung out and incinerated after use to reduce waste or for fuels blending
- Rolls are ideal for covering large areas and soaking up leaks and overspray
- Easy-tear perforations let you take only what you need, so you use less mat and save money
- Medium-weight construction is versatile for general, everyday tasks and cleanups
- Mats take on the properties of absorbed liquids
 - always take proper precautions when handling saturated absorbents



Specifications

| | |
|-----------------------|-----------------------------|
| Dimensions | 30" W x 150' L |
| Mat Weight | Mediumweight |
| Absorbency | Up to 32 gal. per bag |
| Absorbency per | Up to 32 gal. per roll |
| Brand | PIG |
| Category | PIG® Oil-Only Absorbent Mat |
| Color | White |
| Core Diameter | 1.5" |

| | |
|------------------------------------|---|
| Floating | Yes |
| Flammability Specifications | Flame Resistant - Will melt and self-extinguish |
| Fluid Absorbed | Oils; Fuels; Oil-Based Liquids (Not Water) |
| Incinerable | Yes |
| Indoor/Outdoor | Indoor Use; Short-Term Outdoor Use |
| Perforated | Yes |
| Perforated Pattern | 10" x 15" sections |
| Reusable | No |
| Static-Dissipative | No |
| Traffic | Light Foot Traffic |
| UV Resistant | No |
| Wringable | Yes |
| Distributor Part Number | 30ra32;3906102;04088x00046 |
| Sold as | 1 roll per bag |
| Weight | 23 lbs. |
| # per Pallet | 16 |
| Composition | Polypropylene |
| UNSPSC | 47131901 |
| Pigalog® Page Number | Page 43 |

Metric Equivalent

| | |
|-----------------------|------------------------|
| Absorbency | Up to 121.1 L per bag |
| Absorbency per | Up to 121.1 L per roll |
| Dimensions | 76.2cm W x 46m L |
| Weight | 10.4 kg |

Technical Information

Technical Documents

[SPCC: 8 Things You Need to Know](#)

[PIG® Oil-Only Absorbents](#)

[29 CFR 1910.22\(a\)\(2\)](#)

[40 CFR 112.7](#)

[40 CFR 122.26](#)

