

53723

Pipe Exterior Brush, Ø55 mm, 360 mm, Medium, Blue



Keep pipework free of dust and contaminants with this Pipe Exterior Brush, featuring an adjustable head for cleaning pipes with an outside diameter of up to 100 mm.

Technical Data

Item Number	53723
Material	Polyester Stainless Steel (AISI 304) Polypropylene
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Complies with UK 2019 No. 704 on food contact materials	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of phthalates and bisphenol A	No
Is Halal and Kosher compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	320 Pcs
Quantity Per Layer (Pallet)	40 Pcs.
Box Length	545 mm
Box Width	270 mm
Box Height	220 mm
Product Diameter	55 mm
Length	360 mm
Width	200 mm
Height	55 mm
Net Weight	0,16 kg
Weight bag	0,01 kg
Weight cardboard	0,0262 kg
Tare total	0,0362 kg
Gross Weight	0,2 kg
Cubik metre	0,00396 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature³	-20 °C
Max. drying temperature	100 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705022002616

GTIN-14 Number (Box quantity)	15705028002648
Customs Tariff No.	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact
3. Do not store the product below 0° Celsius.