

53763

Tube Brush, Ø20 mm, 500
mm, Medium, Blue



Effectively clean bottles, tubes and hard-to-reach surfaces such as gaps and crevices on machinery and conveyer belts with this handy Tube Brush.

Technical Data

Item Number	53763
Visible bristle length	9 mm
Material	Polypropylene Polyester Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Complies with UK 2019 No. 704 on food contact materials	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of phthalates and bisphenol A	No
Is Halal and Kosher compliant	Yes
Design Registration No.	EU 002175075-1-2
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	2700 Pcs
Quantity Per Layer (Pallet)	150 Pcs.
Box Length	525 mm
Box Width	150 mm
Box Height	105 mm
Product Diameter	20 mm
Length	500 mm
Width	25 mm
Height	25 mm
Net Weight	0,08 kg
Weight cardboard	0,029 kg
Tare total	0,029 kg
Gross Weight	0,11 kg
Cubik metre	0,000313 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature³	-20 °C
Max. drying temperature	100 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH

Gtin-13 Number	5705020537639
GTIN-14 Number (Box quantity)	15705020537636
Customs Tariff No.	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact