

70476

High-Low Brush, 265 mm, Medium, Yellow



Effectively clean and scrub floor-wall junctions and under machines and equipment with this High-Low Brush, featuring an angled thread that lets you use the brush with the handle positioned parallel to the floor. Also ideal for cleaning drains and gulleys.

Technical Data

Item Number	70476
Visible bristle length	41 mm
Material	Polypropylene Polyester Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Complies with UK 2019 No. 704 on food contact materials	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of phthalates and bisphenol A	No
Is Halal and Kosher compliant	Yes
Design Registration No.	EU 002533729-1-5
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	320 Pcs
Quantity Per Layer (Pallet)	40 Pcs.
Box Length	610 mm
Box Width	290 mm
Box Height	200 mm
Length	265 mm
Width	150 mm
Height	100 mm
Net Weight	0,5 kg
Weight bag	0,0078 kg
Weight cardboard	0,0522 kg
Tare total	0,06 kg
Gross Weight	0,56 kg
Cubik metre	0,003975 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature ³	-20 °C
Max. drying temperature	100 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH

Gtin-13 Number	5705020704765
GTIN-14 Number (Box quantity)	15705020704762
Customs Tariff No.	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact
3. Do not store the product below 0° Celsius.