

29362

# Fibre Glass Handle, 1310 mm, Green



This handle is mainly used in areas where high concentration caustic cleaning solutions are used. It can be used with all brooms, squeegees and scrapers. The handle with the attached item should reach to the chin of the user to prevent occupational back injuries. It can also be attached to wall cleaning products to reach up to approximately 3.3m.

# Technical Data

Item Number	29362
Complies with (EC) 1935/2004 on food contact materials <sup>1</sup>	No
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Use of phthalates and bisphenol A	No
Is Halal and Kosher compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	960 Pcs
Quantity Per Layer (Pallet)	0 Pcs.
Box Length	1345 mm
Box Width	190 mm
Box Height	75 mm
Product Diameter	31 mm
Length	1310 mm
Width	31 mm
Height	31 mm
Net Weight	0,49 kg
Weight cardboard	0,028 kg
Tare total	0,028 kg
Gross Weight	0,52 kg
Cubik metre	0,001259 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature <sup>3</sup>	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Symbol "7", Miscellaneous Plastics	No
Gtin-13 Number	5705020293627
GTIN-14 Number (Box quantity)	15705020293624
Customs Tariff No.	96039010
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.