



PD7300 SERIES

PODIUM

375lb

LOAD CAPACITY

TYPE IA DUTY RATING

Combined Weight of User and Materials

INCREASE PRODUCTIVITY

- Fully braced steps
- Built-in toe guard
- Ideal for fixed heights



FOR USE
NEAR ELECTRICITY



WORK FACING ANY DIRECTION.



LOCKTOP™ secures tools and accessories



Extra-large platform for all-day comfort



36 in. high extended guard rail



PD7300 SERIES

375lb
LOAD CAPACITY
TYPE IA DUTY RATING
Combined Weight of User and Materials

- LOCKTOP™ guard rail with lock-in accessory system
- Podium platform with raised toe guard
- Double riveted slip-resistant steps
- EDGE360™ bracing
- Fully braced steps

Guard rail with lock-in accessories

Up to

SPECIFICATIONS

Model No.	Platform Height	Reach Reach†	Straight Ladder Height	Approx. Ladder Length	Approx. Product Width
PD7302	2ft	8ft	4ft	58in	24in
PD7303	3ft	9ft	5ft	69.5in	26in
PD7304	4ft	10ft	6ft	81in	27.5in
PD7305	5ft	11ft	7ft	92.25in	29.25in
PD7306	6ft	12ft	8ft	104in	31in
PD7307	7ft	13ft	9ft	115in	33in
PD7308	8ft	14ft	10ft	126.5in	34.5in
PD7310	10ft	16ft	12ft	149.5in	38in
PD7312	12ft	18ft	14ft	172.5in	41.5in

DIMENSIONS

Platform	16in x 19.5in	Rear Rails	1-7/8in
Front Rails	3-1/8in	Rear Flange	1-3/16in
Front Flange	1-3/16in	Steps	3in

Slip-resistant Traction-Tred® Steps

EDGE360™ bracing



*Number of rear horizontal braces varies by model