

MOBILE WIRE SPOOL & MAINTENANCE CART

Mobile Wire Spool Rack

- Heavy duty, all welded 14 gauge steel
- 1,200 lbs. total capacity
- 1-1/2" lip on top work surface prevents parts from falling off during transport
- Louvered panels on 2 ends, accommodate Hook-On-Bins® and metal Hook-On Trays (Bins and Trays sold separately)
- Heavy duty handle makes transport easy
- (8) 23" removable rods accommodate wire spools
- 7-1/2" between rods, larger spools can be accommodated if some rods are removed
- Recessed rods allow protection of spools during transport
- 4 wire guides hang below the work surface for ease in cutting wire
- (4) 5" x 1-1/4" polyurethane bolt on casters; (2) rigid and (2) locking swivel
- Ships fully assembled
- Durable gray, textured powder coat finish



Model	Overall Dim: WxDxH (In.)	Description	Ship Wt. (Lbs.)
MWSR8-LP-95	18-1/8 x 32-1/4 x 46-1/16	8-Rod Mobile Wire Spool Rack w/2 sides of louvered panels	112

FOB TX

*Handle adds 6" to width

Hook-On Trays not included

**Model
MWSR8-LP-95**

Mobile Wire Spool & Maintenance Cart



- Heavy duty, all welded, 14 gauge steel
- 1,200 lbs. total capacity
- 1-1/2" lip on top work surface prevents parts from falling off during transport (3 sides)
- Louvered panel on end, accommodates Hook-On Bins® and metal Hook-On Trays (Bins and Trays sold separately)
- Heavy duty tubular handle makes transport easy
- (5) 16-1/2" removable rods accommodate wire spools
- Recessed rods allow protection of spools during transport
- Low profile hanger positioned on back holds up to a 6' ladder in the upright
- Has provision to handle boxes of light bulbs, conduit, pvc, or other bulk items
- (4) 5" x 1-1/4" polyurethane bolt on casters; (2) rigid and (2) locking swivel
- Ships fully assembled
- Durable gray, textured powder coat finish

Model	Dimensions: WxDxH (In.)	Carton Pack	Ship Wt.
MWSR5-95	Overall Dimensions: 24 x 54-1/16 x 35 Cabinet: 16-3/8 x 23-7/8 x 22-5/8 Work Surface: 36 x 24	1	196 lbs

Accessories

DSH-184-95	17-1/4 x 3-3/4	6	16 lbs
PB30210-21 - Red Hook-On-Bins®	4 x 5 x 3	24	5 lbs
PB30210-52 - Blue Hook-On-Bins®			
PB30210-17 - Yellow Hook-On-Bins®			

FOB TX

Note: Width and length are based on usable space. The handle will add between 6" - 6-1/2" unless otherwise specified.

Created: 4/9/2018

MAINTENANCE CART



Model
2211-DLP-6DR-RM-9B-95

Mobile Maintenance Cabinet with Drawer & Lockable Storage Compartment

(1,200 lbs. capacity) - Includes 9 Yellow Hook-On-Bins®

- 16 gauge all welded steel construction
- Top surface back stop
- Door has 3-point locking system with fold down pad-lockable handle. Locking hinge is also provided to lock all drawers at once
- Drawers move smoothly on bearing slides
- Convenient sturdy work surface is covered with a black rubber mat
- Ergonomic tubular handle
- Has provision to handle boxes of light bulbs, conduit or pvt.
- Back low profile hanger holds one 6' ladder in an upright position
- Louvered panels on door accommodate Hook-on® Bins
- Hook-On Bins Dimensions: (9) 4"W x 5"D x 3"H
- 5" x 1-1/4" polyurethane casters; (2) swivel and (2) rigid
- Ships fully assembled
- Durable, gray, textured powder coat finish

Model	Overall Dim: WxDxH (In.)	Drawer Dim: WxDxH (In.)	Ship Wt. (Lbs.)
2211-DLP-6DR-RM-9B-95	22-3/16 x 54-1/16 x 41-1/8	(2) 20-7/16 x 14-11/16 x 4-7/8 (4) 20-7/16 x 14-11/16 x 2-7/8	236

FOB TX