

LONG REACH RETRIEVERS



Ideal for reaching behind, underneath or around machinery and/or difficult to reach areas. These tools have a maximum temperature of 300°F (148°C). The MX3000WAH lightweight long reach retriever has a round magnet at a 45 degree angle. The MM06X38 is a long retriever for narrow areas with a rectangular magnet.



Lift - lbs (kg)	Magnet (in)	Length (in)	Weight (lbs)	Model No.
47.5 (21.55)	3-1/4 Diameter	38	1.70	MX3000WAH
8.0 (3.63)	1-3/8 x 6	40	3.00	MM06X38

ON/OFF MAGNETIC UTILITY LIFTER

Stop bending over to lift and move steel pieces and scrap.

Reduce finger and toe injuries with this lightweight deep reach permanent magnetic lifter.

This Magnetic Utility Lifter has a locking On/Off handle for safety and makes moving steel quick and easy.



Lift - lbs (kg)	Height (in)	Width (in)	Length (in)	Weight (lbs)	Model No.
50.0 (22.68)	28-1/2	5-1/2	3-1/2	7.65	MCLVB01
75.0 (34.02)	28-1/2	7	5	14.35	MCLVB02

INSPECTION MIRRORS - HI-VIS ORANGE



These telescoping mirrors have a slim profile, joints that can swivel and/or rotate and have highly visual orange grips and/or heads. Never leave a tool behind! 301G240HVO had a retrieving magnet at the opposite end that can lift 2 lbs and has a handy pocket clip. IMS123HVO contains a stainless steel mirror for use in critical areas where foreign objects cannot be left behind. FOD (Foreign Object Debris) free. Handles are nonslip, solvent resistant cushion grips.



Style	Mirror (in)	Mirror	Shaft Material	Length (in)	Ext. Length (in)	Weight (lbs)	Model No.
A	2 x 1	Glass	Stainless Steel	6-1/2	36	0.17	315HVO
B	2 x 2	Glass	Chrome Plated Brass	6-1/4	28	0.10	301G240HVO
C	3-1/2 x 2-1/2	Glass	Stainless Steel	7-1/4	37	0.21	318HVO
D1	2-1/4 Dia	Glass	Stainless Steel	7	36-1/2	0.20	309S1HVO
D2	2-1/4 Dia	Stainless	Stainless Steel	7	36	0.15	IMS123HVO
E	2 x 2	Acrylic	Stainless Steel	7	35-1/2	0.21	312AHVO

LIGHTED INSPECTION MIRROR



This telescoping glass mirror contains 3 LED lights that pivot to shine the light exactly where you need it. Mirror is on a double ball joint. Batteries included.

Replacement batteries: 2pc CR2032 Lithium



Mirror (in)	Mirror	Shaft Material	Handle/Grip Feature	Length (in)	Extended Length (in)	Weight (lbs)	Model No.
2-3/4 x 1-7/8	Glass	Stainless Steel	Non-slip, Solvent Resistant	7-1/2	35	0.25	IMG238L

INSPECTION TOOL KITS



Best of both worlds when you package a telescoping mirror or magnifier with a telescoping Rare Earth magnetic retriever in a foam-lined snap-lock case. These tools have a nonslip, solvent-resistant grip.

Note: MMK200 is Non-telescoping, Non-conductive (Nylon construction, including the grip), and does not come in a case. MMK301 contains a Lighted Magnetic Pick-up Tool, 4-Jaw, 7/16" dia., 8-3/4" Mechanical Finger retriever and a Round Magnifying Inspection Mirror.



Mirror / Magnifier (in.)	Mirror	Lift - lbs (kg)	Shaft Material	Mirror / Magnifier Length (in)	Magnet Diameter (in)	Magnet Head	Magnet Length (in)	Weight (lbs)	Model No.
1-1/2 dia.	Glass	1 (0.45)	Nylon	8-1/4	5/16	Swivel	8-1/4	0.05	MMK200
1-3/4 x 2-1/2	Acrylic	14 (6.35)	Stainless	7-1/2 - 34	5/8	Fixed	7-1/2 - 34	0.60	MMK201
1-3/4 x 2-1/2	Acrylic	14 (6.35)	Stainless	7-1/2 - 34	5/8	Swivel	7-1/2 - 34	0.60	MMK203
1-3/4 x 2-1/2	3X Glass Magnifier	14 (6.35)	Stainless	7-1/2 - 34	5/8	Swivel	7-1/2 - 34	0.60	MMK204
2-1/2 dia.	3X Glass	22 (9.97)	Stainless	7 - 36	11/16	Lighted/Fixed	7-1/2 - 32	0.90	MMK301