



**U.S. Tsubaki Power Transmission, LLC**

301 E. Marquardt Dr.

Wheeling, IL 60090

**Phone:** 847.459.9500 or 800.323.7790

**Fax:** 847.459.9515

**Email:** [sales@ustsubaki.com](mailto:sales@ustsubaki.com)

**Website:** [www.ustsubaki.com](http://www.ustsubaki.com)

## NO. 40 - 1/2" PITCH - TAPER-LOCK® SPROCKETS

TAPER-LOCK® is a registered trademark of Rockwell Automation.



1 2

<u>Item #</u>	<u>Style</u>	<u>Chain Size</u>	<u>No. Teeth</u>	<u>Outside Diameter</u>	<u>Max. Bore</u>	<u>Weight</u>	<u>Quantity</u>
<a href="#"><u>40BTL14</u></a>	B	40	14	2.491 in	1.000 in	0.300 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL15</u></a>	B	40	15	2.652 in	1.000 in	0.400 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL16</u></a>	B	40	16	2.814 in	1.000 in	0.500 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL17</u></a>	B	40	17	2.975 in	1.250 in	0.500 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL18</u></a>	B	40	18	3.135 in	1.250 in	0.600 lb	<input type="text" value="1"/>

<b>Item #</b>	<b>Style</b>	<b>Chain Size</b>	<b>No. Teeth</b>	<b>Outside Diameter</b>	<b>Max. Bore</b>	<b>Weight</b>	<b>Quantity</b>
<a href="#"><u>40BTL19</u></a>	B	40	19	3.296 in	1.250 in	0.700 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL20</u></a>	B	40	20	3.457 in	1.625 in	0.700 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL21</u></a>	B	40	21	3.617 in	1.625 in	0.800 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL22</u></a>	B	40	22	3.778 in	1.625 in	0.900 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL23</u></a>	B	40	23	3.938 in	1.625 in	1.000 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL24</u></a>	B	40	24	4.098 in	1.625 in	1.400 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL25</u></a>	B	40	25	4.258 in	1.625 in	1.500 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL26</u></a>	B	40	26	4.418 in	1.625 in	1.700 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL28</u></a>	B	40	28	4.738 in	1.625 in	1.800 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL30</u></a>	B	40	30	5.057 in	1.625 in	1.900 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL32</u></a>	B	40	32	5.377 in	1.625 in	1.900 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL35</u></a>	B	40	35	5.855 in	1.625 in	2.300 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL36</u></a>	B	40	36	6.015 in	1.625 in	2.400 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL40</u></a>	B	40	40	6.653 in	1.625 in	2.800 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL42</u></a>	B	40	42	6.972 in	1.625 in	2.900 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL45</u></a>	B	40	45	7.451 in	1.625 in	3.500 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL48</u></a>	B	40	48	7.928 in	1.625 in	4.000 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL54</u></a>	B	40	54	8.885 in	1.625 in	4.900 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL60</u></a>	B	40	60	9.841 in	1.625 in	6.000 lb	<input type="text" value="1"/>
<a href="#"><u>40BTL70</u></a>	B	40	70	11.434 in	2.000 in	8.200 lb	<input type="text" value="1"/>

<u>Item #</u>	<u>Style</u>	<u>Chain Size</u>	<u>No. Teeth</u>	<u>Outside Diameter</u>	<u>Max. Bore</u>	<u>Weight</u>	<u>Quantity</u>
---------------	--------------	-------------------	------------------	-------------------------	------------------	---------------	-----------------