

GE 710 Compact (600615420) Die Grinder
Cardboard box

Order no. 600615420
EAN 4007430212344



Representative picture



- Particularly handy due to the compact design
- Vario-Constamatic (VC)-Full wave electronics for working at customized speeds to suit the application materials, and speeds that remain almost constant even under load
- Thumbwheel for speed preselection
- Electronic safety shutdown of the motor for safe working in case the tool stops unexpectedly
- Restart protection: prevents unintentional start-up after power supply interruption
- Electronic overload protection for long service life
- Precise collar for stationary use
- Slim housing for ideal handling
- Precision collet for precise concentricity
- Metabo Long-life motor with patented dust protection for long service life

Technical values

Parameters

No-load speed	13000 - 34000 RPM
Amps	6.4 AMPS
Rated input power	710 W
Output power	430 W
Revolutions at rated load	24000 RPM
Collar diameter	1 11/16 "
Collet chuck bore	1/4 "
Weight (without power cable)	3.1 lbs
Cable length	9 ft

Vibration

Grind surface (up to Ø 25 mm)	6.8 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	82 dB(A)
Sound power level (LwA)	93 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Collet 1/4"

2 open-end wrenches