

W 850-125 (603608420) Angle Grinder
(110-120 V / 50 - 60 Hz); Cardboard box

Order no. 603608420
EAN 4007430338037



Product may differ from Image

- Robust, universal and economical: powerful angle grinder for any application
- Powerful motor with good overload capacity
- Twist-proof guard

Technical data

Characteristics

Disc-Ø	115 / 125 mm // 4 1/2 / 5 "
Rated input power	850 W
Output power	520 W
No-load speed	11500 rpm
Revolutions at rated load	7000 rpm
Torque	2 Nm / 18 in-lbs
Spindle thread	5/8" - 11 UNC
Weight (without power cable)	1.8 kg / 4 lbs
Cable length	2.5 m / 8 ft

Vibration

Surface grinding	8 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Grinding with sandpaper	2.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	88 dB(A)
Sound power level (LwA)	99 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Guard
Side handle
Flat-pin spanners
Inner support flange
Nut with two holes