

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

70-215

Medium duty cut resistant gloves

Previously known as: Neptune[®]Kevlar[®]70-215



Cut



Heavy Duty

Superior mechanical protection and cut-resistance

- The 100% Dupont Kevlar[®] construction offers a very high cut resistance to weight ratio. The use of Terry loop technique enhances heat insulation. The resulting thicker-walled glove offers high shock absorption without losing dexterity
- Thanks to the Neptune[®] coating the glove fibres repel liquids, avoiding damage to the Kevlar[®] strands and extending glove life.
- The reinforced thumb welt increases abrasion resistance also adding to glove durability. The ambidextrous gloves are fully washable and can be re-used many times



Industries

- Automotive
- Machinery and Equipment

Applications

- Metalworking & assembly operations
- Chassis assembly, body trimming
- Seizing structural and body parts
- Inspection (picking, checking and marking)
- Touching up

HyFlex®

ADVANCED MECHANICAL PROTECTION

70-215

Medium duty cut resistant gloves

Previously known as: Neptune®Kevlar®70-215

Key Features

- 100% DuPont™ Kevlar® glove provides light-duty cut protection
- Protection from sharp edges of metals, ceramics, glass and other materials
- Reversible design allows glove to be worn on either hand, reducing replacement costs
- Launderable

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex® 70-215	Coating Material: N/A Liner Material: Kevlar® Cuff Style: Knitwrist	7	7, 8, 9, 10	230 - 280 mm/ 8.5-10.23 inches	• 12 pairs in a bag; 12 bags in a carton

Technologies

Kevlar®

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.