

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-731

Enhanced comfort, durability and
INTERCEPT[®] Cut Resistance
Technology



Cut

Lasts up to 2x longer for extended wear with high levels of cut protection

- Combination of ultra-lightweight comfort and ISO cut level B Ansi Cut 2 performance
- High abrasion resistance (EN level 4) with high dexterity for precision handling of sharp, small parts
- Designed using Ansell's exclusive proprietary yarns, making it a best-in-class value
- Light weight second-skin liner design to support comfort and tactility



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Transportation

Applications

- Assembly & inspection of components
- Press injection molding
- Picking, fastening components
- Final assembly
- Delivery of parts to production line
- Applying finish to materials, products
- Handling incoming goods

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-731

Enhanced comfort, durability and
**INTERCEPT[®] Cut Resistance
Technology**

Key Features

- Light Duty 18 gauge seamless liner provides enhanced flexibility (range of motion) & tactility (fingertip sensitivity)
- Thin PU coating provides high dexterity with high abrasion resistance (EN level 4)
- Dirt-Masking coating color hides dirt in environments with dirt exposure
- Also available in vend pack

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex [®] 11-731	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Fiber glass, HPPE, Nylon, Spandex Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	212-277 mm/ 8,34-10,43 inch	Grey	• 12 pairs/bag; 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

