



Cut



Medium Duty

Extreme resistance to cuts and burrs. good fit, flexibility & cool feeling

- Ansell's HyFlex 11-435 glove is the first cut-resistant ISO Cut level C on the market made with water-based polyurethane & NBR
- Resistance to cuts and burrs. A seamless plaited glove for very good fit, dexterity and flexibility. Excellent breathability and cool feeling
- Water-based polyurethane & NBR enhances the dexterity and comfort of the glove, as the polyurethane doesn't penetrate inside it



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Body painting including surface inspection
- Chassis assembly, body trimming
- Mounting and dismantling
- Foundry operations
- Handling materials with sharp or rough edges
- Fastening components, parts
- Maintenance

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-435

Unmatched dexterity and high cut protection With Waterbased PU & NBR coating

Key Features

- Unique combination of Dyneema®, Nylon, Lycra®, and glass fiber
- Ultra strong fibers provide extreme resistance to cuts and burrs
- Anti-static for improved safety in critical areas
- Silicone free
- Oeko-Tex® 100 approved
- Also available in vend pack

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-435	Finishing: Palm Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Nylon, Lycra®, Fiber glass, Dyneema® Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	225-275 mm; 8.85-10.82 inches	Black	<ul style="list-style-type: none"> • 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

