

These chemical protective gloves offer an unrivaled combination of chemical resistance, confident grip, and a comfortable inner lining that make this glove ideal for outdoor application

These chemical protective and oil-resistant waterproof gauntlet gloves offer a unique combination of liquid-proof chemical resistance and grip, together with flexibility and dexterity, making this glove the logical choice when working with chemicals.

Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Metalworking & assembly operations
- Body painting including surface inspection
- Applying sealers, touching up
- Changing tools and dies
- Handling application & cleaning tools
- Warehousing of raw materials
- Loading and unloading trucks and vehicles
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Opening furnaces draining pumps valves or lines and crackers BTX process



Key Features

- The glove incorporates revolutionary ANSELL GRIP™ technology to enable users to handle wet or oily objects using less force to grip, providing more control. This unique combination of liquid proof chemical resistance and grip, together with flexibility and dexterity, makes the AlphaTec glove the logical choice when working with chemicals.
- Reliable chemical protection for added user safety. The bonded construction ensures that the coating polymer does not penetrate the liner during manufacture. The coating is therefore consistent and sound, significantly reducing the likelihood of chemical leakage onto the skin
- 58-530B with black acrylic liner are recommended for outdoor applications

Technologies



ANSELL GRIP™
Ansell Grip Technology



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-530B	Acrylic, Nitrile, Ansell Grip™	7	7, 8, 9, 10, 11	290-316 mm/ 11-12 inches	Grey	• 6 pairs/polybag; 12 polybags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.