

These gloves are chemical and cut-resistant so you don't have to compromise between chemical and cut protection, have both!

- These nitrile grip gloves offer a nitrile barrier that provides advanced chemical protection from many frequently used chemicals
- AlphaTec® 58-735 chemical and cut-resistant gloves have 'Type A' chemical protection under new EN ISO 374:2016, cut level 'ISO C' according to EN 388:2016
- ANSELL GRIP™ Technology for the handling of wet or oily parts providing enhanced dexterity, grip and comfort
- For complete chemical permeation information, please visit: www.ansellguardianpartner.com

Industries

- Automotive
- Chemical
- Life Sciences
- Machinery and Equipment
- Oil and gas
- Food Processing
- Metal fabrication
- Emergency Medical Services

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Filling, blending and charging of raw materials
- Sample taking and processing
- Removal of broken glassware
- Spill or leakage cleanup
- Assembling and mounting components
- Mixing or loading chemicals
- Cleaning of plant and machines
- Handling application & cleaning tools



Key Features

- INTERCEPT™ Cut Resistant Technology provides protection against lacerations
- Optimised fit that integrates the cut liner into nitrile shell for better dexterity & tactility versus double gloving
- Excellent dry & wet grip enhance dexterity and reduce hand fatigue
- Yellow high-visibility cut liner acts as an indicator for when glove is cut, highlighting when chemical protection is compromised
- Cuff can be folded to act as a gutter to prevent chemicals running down the arm
- Oeko-Tex® Standard 100 Approved
- Compliant with FDA food handling requirements

Technologies



ANSELL GRIP™
Ansell Grip Technology



INTERCEPT™
Cut Resistance Technology



Performance Standards



EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-735	Ansell INTERCEPT™ Technology, Nitrile, Ansell Grip™	18	6, 7, 8, 9, 10, 11	350 mm	Medium Glass Green	• 6 pairs/bag; 12 bags/case

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.