

HyFlex®

ADVANCED MECHANICAL PROTECTION

48-101

Designed for light applications that require good levels of comfort and abrasion resistance

Previously known as: Sensilite®



Multi Purpose



Light Duty

Comfort and protection for lightweight applications

- Designed for light applications that require good levels of comfort and abrasion resistance
- Offering precise handling of small objects in dry or light oily environments, HyFlex® 48-101 is the practical choice when you are looking for dexterity
- HyFlex® 48-101 provides enhanced safety, dexterity and durability compared to other glove options often used in the same applications



Industries

- Automotive
- Machinery and Equipment

Applications

- Chassis assembly, body trimming
- Production line support & maintenance
- Equipment repair & maintenance
- Assembly and disassembly of equipment
- Loading and unloading rough parts or boxes
- Picking parts and accessories

Previously known as: Sensilite®

Key Features

- Excellent abrasion resistance for an extended wear life
- Thin liner and coating offering great dexterity and flexibility
- HyFlex® 48-101 allows extreme tactility where precision is required
- Also available in vend pack

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 48-101	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Nylon Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	220-270 mm/ 8.66-10.63 inches	Black	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.