TLR-8® HL-X SUB

MULTI-FUEL, HIGH-LUMEN, HIGH CANDELA LIGHT WITH RED LASER FOR SUBCOMPACT RAILED HANDGUNS



High Switch



Low Switch





Available Colors:

The TLR-8 HL-X sub multi-fuel, rail-mounted light with red laser accepts either an SL-B9® USB rechargeable protected lithium-ion battery pack or a CR123A lithium battery. Includes high and low paddle switches to match your shooting style.

OUTPUT

	SL-B9 (DEFAULT)	SL-B9 (PROGRAMMABLE)	CR123A
LUMENS	1,000	500	500
CANDELA	10,000	5,000	5,000
DISTANCE	200m	141m	141m
RUN TIME	30 min	1 hr	1.5 hrs

Laser mode runs 29 hours

ITEM NUMBERS

Description	UPC	Item #
TLR-8 HL-X sub USB (GLOCK® 43X/48 MOS | 43X/48 Rail) - Includes mounting kit with key, multi-tool, (1) SL-B9 battery pack, and USB-C cord	080926-69466-8	69466
TLR-8 HL-X sub USB (SIG SAUER® P365®/XL closed rail systems*) - Includes mounting kit with key, multi-tool, (1) SL-B9 battery pack, and USB-C cord **Does not fit the P365® XMACRO*	080926-69467-5	69467
TLR-8 HL-X sub USB (1913 short) - Includes mounting kit with keys, multi-tool, (1) SL-B9 battery pack, and USB-C cord	080926-69468-2	69468
TLR-8 HL-X sub USB (Springfield Armory® Hellcat®) - Includes mounting kit with key, multi-tool, (1) SL-B9 battery pack, and USB-C cord	080926-69469-9	69469

KEY FEATURES

- Engineered to produce a longer reaching, tighter beam; 1,000 lumens, 10,000 candela
- Front-loading battery capability
- "Safe-off" feature prevents accidental activation, saves batteries
- Interchangeable rear paddle switches

BATTERY

- Multi-fuel: Accepts (1) SL-B9 rechargeable battery pack (included) or (1) CR123A lithium battery
- SL-B9 battery pack charges within 2.5 hours via USB-C cord or bank charger; rechargeable up to 500 cycles

MATERIAL/DURABILITY

- 6000 Series machined aircraft aluminum with black anodized finish
- Switch housing: Impact- and chemical-resistant engineered polymer
- High temperature, shock-mounted, impact-resistant BOROFLOAT® glass lens
- IPX4 water-resistant

DIMENSIONS

LENGTH: 2.51 in (6.38 cm)

WEIGHT: W/ BATTERY — SL-B9 2.87 oz (81.4g) // CR123A 2.77 oz (78.5g)

WARRANTY

Limited lifetime warranty
Visit streamlight.com for full warranty information

ACCESSORIES

	Description	UPC	Item #
	CR123A Lithium Batteries - 2 Pack CR123A Lithium Batteries - 6 Pack CR123A Lithium Batteries - 12 Pack CR123A Lithium Batteries - 400 Pack	080926-85175-7 080926-85180-1 080926-85177-1 080926-85179-5	85175 85180 85177 85179
	SL-B9 USB-C Rechargeable Battery Packs - 2 Pack SL-B9 USB-C Rechargeable Battery Packs - 8 Pack SL-B9 USB-C Rechargeable Battery Packs - 100 Pack	080926-20237-5 080926-20238-2 080926-20239-9	20237 20238 20239
	22” (55.88 cm) USB-C Cord	080926-22084-3	22084
	Tail Cap Assembly	080926-69493-4	69493
	Clamp Jaw Kit - GLOCK® 43X/48 MOS | 43X/48 Rail	080926-69320-3	69320
	Clamp Jaw Kit - Springfield Armory® Hellcat®	080926-69321-0	69321
	Clamp Jaw Kit - 1913 short	080926-69322-7	69322
	Clamp Jaw Kit - SIG SAUER® P365®/XL	080926-69323-4	69323