

Twist-Lock® Devices

20A, 250V; 2 Pole, 3 Wire Grounding

Screwless Terminated InsulGrip® Connector



- Features
- Faster termination time
 - No need for screwdriver and torque wrench
 - Spring Termination eliminates strand relaxation
 - Funnel shaped wire entry for ease of termination.
 - Superior cord grip design protects terminations from excess strain

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Black and white nylon.	.360"-.930" (9-24)	78358571926	HBL2323ST

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

Housing / Cord Clamp	Nylon
Terminal Retainer	Nylon
Plunger	Nylon
Contacts	Brass
Terminal Spring Clamp	Spring Steel
Assembly Screws	Zinc Plated Tri-drive
Weight (lbs)	0.35

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 3,000V minimum
Mechanical	
Terminal Accommodation	#14 AWG - #8 AWG stranded copper wire only
Terminal Identification	Terminals identified in accordance with UL 498
Environmental	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C, Minimum -40°C (w/o impact)



Online Resources

Customer Sales Drawings
eCatalog

