

Ansell

NEW PRODUCT SPOTLIGHTS

SAFETY SOLUTIONS FOR EVERY SITUATION

ABRASION, CUT & ERGONOMIC PROTECTION

HyFlex® 11-842

Our best multi-purpose gloves, now made green

- **90% recycled nylon liner*:** Carbon footprint reduction of 75g CO₂eq/pair**
- **FORTIX™ Technology:** Up to 20% greater abrasion resistance[^]
- **ZONZ™ Comfort Fit Technology:** Better breathability and hand movement

* Minimum recycled content of 30% in the final product (based on size 9)

** Vs standard nylon multi-purpose glove

[^] Vs previous technology version



Size	MSC#	Size	MSC#
5	60070133	9	60070059
6	60070042	10	60070083
7	60069770	11	60070166
8	60070075	12	60070141

HyFlex® 11-645

Mechanical protection gloves granting superior cut resistance and optimal comfort

- **INTERCEPT™ Cut Resistance Technology:** Twice the cut resistance*
- **Fit and feel of an ANSI A2/ISO B-rated glove:** Enhanced comfort
- **PU coating**:** High durability for dry and slightly oily applications

* Versus similar gloves made of standard HPPE yarn

** Low DMF content <100ppm compared to industry standard <1000ppm



Size	MSC#	Size	MSC#
5	56931173	9	56555600
6	56554355	10	56549553
7	56931181	11	56578826
8	56554769	12	56554777

HyFlex® 11-571

The lightest ISO D/ANSI A4-rated cut resistant glove* offering 20% greater durability**

- **Ultra-lightweight design:** Delivers 20% lighter* ISO D/ANSI A4 cut level, up to 20% greater durability**
- **EN ISO D/ANSI A4 cut protection:** 2x greater cut resistance***
- **Thumb crotch reinforcement:** Ideal for dry and slightly oily applications

* Versus standard EN ISO D/ANSI A4-rated gloves

** Versus previous technology version

*** Versus similar gloves made of standard HPPE yarn



Size	MSC#	Size	MSC#
5	56932866	9	56932874
6	56555592	10	56554975
7	56931660	11	56931652
8	56578560	12	56554983

HyFlex® 11-561

The thinnest, lightest EN ISO C/ANSI A3-rated cut resistant gloves, offering up to 20% greater durability*

- **FORTIX™ Technology:** Up to 20% greater abrasion resistance*
- **INTERCEPT™ Technology:** Ultra-lightweight design delivers 20% lighter** ISO C/ANSI A3 cut level resistance
- **Palm-dipped coating:** For breathable PPE gloves with superior grip

* Versus previous technology version

** Versus standard EN ISO C/ANSI A3-rated gloves



Size	MSC#	Size	MSC#
5	-	9	-
6	-	10	-
7	-	11	-
8	-	12	-

HyFlex® 11-543

Durable, versatile cut-resistant gloves, specially designed for demanding applications

- **INTERCEPT™ Technology:** EN ISO F/ANSI A7 cut resistance
- **FORTIX™ Technology:** Excellent abrasion resistance
- **EN 407 contact heat level 1:** Hand protection up to 100°C/212°F



Size	MSC#	Size	MSC#
6	06532139	9	06522692
7	06532121	10	06532238
8	06522700	11	06532220

Click on an item code to view the product

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. © 2024 Ansell Limited. All Rights Reserved.

Call MSC today to learn about the latest featured styles from Ansell
800.645.7270 | mscdirect.com/ansell

Available
Today At

MSC