



Multi Purpose Abrasion Protection



Light Duty

Abrasion-resistant gloves, combining durable hand coverage with assured grip and tactility

- **Improved practicality:** These black work gloves conceal dirt and grime and are discarded less quickly, thereby providing a more cost-effective solution
- **Increased protection:** EDGE[®] 48-126 protective gloves are composed of a seamless knitted liner and an elasticized knitwrist that are reinforced by black polyurethane coating, which offer better flexibility and dexterity than cotton canvas and thick cotton gloves
- **Enhanced comfort and dexterity:** EDGE[®] 48-126 safety gloves are made of a 15-gauge polyester liner that meets workers' needs in terms of comfort and flexibility



Industries

- Automotive
- Electronics
- Machinery and Equipment
- Oil and gas
- Transportation
- Utilities

Applications

- Assembly of small pieces
- General handling
- Packaging
- Quality inspection

Key Features

- **Black exterior:** Economical industrial gloves with longer wear life
- **Seamless design:** Form-fitting, high-dexterity hand protection gloves
- **15-gauge polyester liner:** For assured hand comfort and flexibility

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



4121A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 48-126	Finishing: Palm dipped Coating Material: Polyurethane Liner Material: Polyester Cuff Style: Knitwrist	15	6, 7, 8, 9, 10, 11	215-270 mm, 8.46-10.63 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.