

The best of both hygiene & efficiency

Vikan squeegees



Unique products for unique challenges



Ultra Hygiene Squeegee



Double Blade Ultra Hygiene Squeegee



Double Blade Foam Squeegee

Complete range

Vikan squeegees distinguish themselves not only by the high quality of the individual product, but also by the extensive range. It is our conviction that hygiene is optimized when employees have access to the tools that suit both the task and the person best. With the right tools, the job is also carried out more effectively and efficiently.

Select the right squeegee for the job

Our broad range of squeegees cover all needs for professional cleaning where hygiene is essential. The selection spans from flexible and functional models with foam rubber to one-piece molded models with double-component rubber. To achieve the highest efficiency and hygiene, it is important to use the right squeegee for the job.

Ultra Hygiene Squeegee




- What:** Ultra hygienic one-piece molded single-blade squeegee.
- Where:** For areas that require the highest level of hygiene.
- Why:** Designed to be effective in use, but also easy to clean with no hiding places for dirt and microbes. It may also be autoclaved at 121°C / 250°C.



Double Blade Ultra Hygiene Squeegee




- What:** A hygienically designed double-bladed squeegee with a replaceable cassette that can be autoclaved at 121°C / 250°C.
- Where:** Highly effective on tiled, uneven anti-slip surfaces where hygiene is essential.
- Why:** The unique design means you do not have to compromise between hygiene & efficiency.




Classic double blade squeegee

- What:** A double blade foam rubber squeegee with replaceable cassette with either fixed or rotating neck.
- Where:** Areas with smooth or tiled surfaces with large amounts of liquid or debris.
- Why:** The most effective squeegee for removing large amounts of liquid or debris quickly and effectively.



Ultra Hygiene Squeegee



With fixed neck

7125	10 in Bench squeegee
7140	16 in
7150	20 in
7160	24 in
7170	28 in

Double Blade Ultra Hygiene Squeegee

With fixed neck

7711	10 in Bench squeegee
7713	20 in
7714	24 in

Replacement cassette

7731	10 in
7733	20 in
7734	24 in

Double Blade Foam Squeegee

With fixed neck

7751	10 in Bench squeegee
7752	16 in
7753	20 in
7754	24 in
7755	28 in

With revolving neck

7763	20 in
7764	24 in

Replacement cassette

7771	10 in
7772	16 in
7773	20 in
7774	24 in
7775	28 in

Fully updated product specifications are available at Vikan.com.

See squeegees online at remcoproducts.com

Available in the U.S. from:

REMCO PRODUCTS CORPORATION

Tel.: (317) 876-9856

Fax: (800) 585-8619

www.remcoproducts.com

sales@remcoproducts.com

7/14 VKN-P104 | Vikan® is a registered trademark of Vikan A/S

