



Multi Purpose



Light Duty

## These breathable nitrile work gloves offer an improved design that delivers up to 30% more breathability. For all day, everyday comfort.

- Ansell ZONZ™ Comfort Fit technology for enhanced fit and improved feel
- More durability vs the original design
- These breathable work gloves benefit from proprietary washing process that efficiently extracts impurities to deliver a cleaner, more comfortable glove
- The improved coating on these breathable nitrile gloves offers improved grip in dry and slightly oily environments along with an extended durability compared to its previous formulation



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

### Applications

- Picking, fastening components
- Adjusting systems and screwing
- Fastening components, parts
- Loading and unloading trucks and vehicles
- Handling incoming goods
- Loading trucks & vehicles
- Product shipping, transport and delivery
- Lock smith

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-800

The Multi-Purpose standard for 20 years, now designed to be even more comfortable

### Key Features

- Our legendary first-to-market foam coating provides more breathability that extends workers' comfort. The foam nitrile coating promotes better grip allowing the worker to perform tactile tasks with ease
- Tailored fit at the base of the pinky finger better matches natural hand contours
- Benefits from proprietary washing process that efficiently extracts impurities to deliver a cleaner, more comfortable glove. Independently certified as skinfriendly by the Oeko-Tex® testing & certification system
- No transfer of silicone contaminants to metal parts prior to painting
- Also available in vend pack

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Technologies



**ZONZ™**  
Comfort Fit Technology

### Specifications

| BRAND   STYLE  | DESCRIPTION                                                                                                                            | Gauge | SIZE           | LENGTH                          | COLOR | PACKAGE                                  |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------|-------|----------------|---------------------------------|-------|------------------------------------------|
| HyFlex® 11-800 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Foam Nitrile<br><b>Liner Material:</b> Nylon<br><b>Cuff Style:</b> Knitwrist | 15    | 6, 7, 8, 9, 10 | 199 - 265 mm/ 7.8 - 10.4 inches | Grey  | • 12 pairs in a bag; 12 bags in a carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

**Ansell**