

ANSI CUT LEVEL GLOVES

The Steiner CR series cut-resistant liner is constructed with a unique design of blended interlocking knit fabric that combines a para-aramid sheath surrounding a high-strength filament core making a stretchable, comfortable lining that provides high cut-level and puncture resistance while maintaining dexterity.



TIG

0261CR

- Premium grain kidskin leather palm with breathable, flame resistant multi-layer cotton back
- Lined with cut and heat resistant para-aramid knit fiber blend
- Meets ANSI ISEA Cut Level A6
- SensiTIG™ seamless index finger
- Leather knuckle strap protection
- Rest patch side reinforcement
- Keystone thumb
- Kevlar sewn
- Sizes S-2X

MSC Part Numbers

- 0261CR-S 99019325
- 0261CR-M 99019226
- 0261CR-L 10705432
- 0261CR-X 10704823
- 0261CR-2X 99019200



TIG

0224CR

- Premium goatskin
- Lined with cut and heat resistant para-aramid knit fiber blend
- Meets ANSI ISEA Cut Level A6
- SensiTIG™ seamless index finger
- Straight thumb for best gun grip
- 4" split cowhide cuff
- Sizes S-2X

MSC Part Numbers

- 0224CR-S 99019341
- 0224CR-M 99019192
- 0224CR-L 99019283
- 0224CR-X 99019184
- 0224CR-2X 99019267

Call MSC today to learn about the latest STEINER solutions.

800.645.7270 | mscdirect.com

Available
Today At

MSC



ANSI CUT LEVEL GLOVES

The Steiner CR series cut-resistant liner is constructed with a unique design of blended interlocking knit fabric that combines a para-aramid sheath surrounding a high-strength filament core making a stretchable, comfortable lining that provides high cut-level and puncture resistance while maintaining dexterity.



MIG

0217CR

- Premium grain cowhide
- Lined with cut and heat resistant para-aramid knit fiber blend
- ANSI ISEA Cut Level A6
- Seamless index finger
- Kevlar® sewn
- Wing Thumb
- 4" split cowhide cuff
- Sizes S-2XL

MSC Part Numbers

- 0217CR-S 99019259
- 0217CR-M 99019333
- 0217CR-L 99019234
- 0217CR-X 99019309
- 0217CR-2X 99019291



MIG

0233CR

- Premium grain cowhide palm with durable split cowhide back
- Lined with cut and heat resistant para-aramid knit fiber blend
- ANSI ISEA Cut Level A6
- Seamless index finger
- Kevlar® sewn
- Straight thumb for best gun grip
- Elastic gathered back snugs hands for comfortable fit
- 3 1/2" split cowhide cuff
- Sizes S-2X

MSC Part Numbers

- 0233CR-S 94102316
- 0233CR-M 94102217
- 0233CR-L 94102332
- 0233CR-X 39952650
- 0233CR-2X 94102225

Call MSC today to learn about the latest
STEINER solutions.

800.645.7270 | mscdirect.com

Available
Today At

MSC

