



COOL TO THE CORE // CHILL-ITS® COOLING VESTS



6665
Evaporative Cooling Vest -
Embedded Polymers, Zipper Closure



6667
Wet Evaporative Cooling Vest -
PVA, Zipper Closure



6668
Hi-Vis Safety Cooling Vest -
Type R, Class 2



6685
Dry Evaporative Cooling Vest -
Zipper Closure



6687
Dry Evaporative Cooling Vest -
Elastic Waist



6215
Premium FR Phase Change Cooling
Vest With Rechargeable Ice Packs



6230
Standard Phase Change Cooling Vest
With Rechargeable Ice Packs



6260
Lightweight Phase Change Cooling
Vest With Rechargeable Ice Packs

COOLING TYPE/ TECHNOLOGY	WET EVAPORATIVE COOLING EMBEDDED POLYMERS	WET EVAPORATIVE COOLING PVA	WET EVAPORATIVE COOLING EMBEDDED POLYMERS	DRY EVAPORATIVE COOLING	DRY EVAPORATIVE COOLING	PHASE CHANGE COOLING	PHASE CHANGE COOLING	PHASE CHANGE COOLING
ENVIRONMENT	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW/MODERATE HUMIDITY AND SUFFICIENT AIRFLOW	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW/MODERATE HUMIDITY AND SUFFICIENT AIRFLOW	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW/MODERATE HUMIDITY AND SUFFICIENT AIRFLOW	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW HUMIDITY AND SUFFICIENT AIRFLOW	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW HUMIDITY AND SUFFICIENT AIRFLOW	HOT INDOOR + OUTDOOR ENVIRONMENTS (NO AIRFLOW REQUIRED)	HOT INDOOR + OUTDOOR ENVIRONMENTS (NO AIRFLOW REQUIRED)	HOT INDOOR + OUTDOOR ENVIRONMENTS (NO AIRFLOW REQUIRED)
HOW TO WEAR	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT
CLOTHING LAYER	OUTER LAYER	OUTER LAYER	OUTER LAYER	OUTER LAYER	OUTER LAYER	OUTER LAYER OR UNDER PPE	OUTER LAYER OR UNDER PPE	OUTER LAYER OR UNDER PPE
COOLING HOURS	UP TO 4 HOURS	UP TO 4 HOURS	UP TO 4 HOURS	UP TO 72 HOURS	UP TO 72 HOURS	UP TO 4 HOURS	UP TO 4 HOURS	UP TO 2 HOURS
ACTIVATION METHODS	SOAK IN WATER	RUN UNDER WATER	SOAK IN WATER	FILL WITH 13-17OZ (400-500ML) OF WATER.	FILL WITH 13.5-15.5OZ (400-450ML) OF WATER	PLACE IN COOLER OF ICE WATER, FREEZER OR REFRIGERATOR	PLACE IN COOLER OF ICE WATER, FREEZER OR REFRIGERATOR	PLACE IN COOLER OF ICE WATER, FREEZER OR REFRIGERATOR
ACTIVATION TIME	2 - 5 MINUTES (MAXIMUM)	1 - 5 MINUTES	2 - 5 MINUTES (MAXIMUM)	IMMEDIATE	IMMEDIATE	10 MINUTES: COOLER OF ICE 15 MINUTES: FREEZER 25 MINUTES: REFRIGERATOR	10 MINUTES: COOLER OF ICE 15 MINUTES: FREEZER 25 MINUTES: REFRIGERATOR	5 MINUTES: COOLER OF ICE 8 MINUTES: FREEZER 12 MINUTES: REFRIGERATOR
PHASE CHANGE TEMPERATURE	--	--	--	--	--	64°F // 18°C	64°F // 18°C	64°F // 18°C
STANDARDS/COMPLIANCE	--	--	ANSI/ISEA 107-2020 TYPE 2, CLASS R	--	--	ASTM F1506 ATPV RATING CAT 1	--	--
POCKETS	--	--	1 CHEST EXTERIOR POCKET 2 LOWER INTERIOR POCKETS PEN POCKET	--	--	PEN POCKET	--	2 LOWER EXTERIOR POCKETS
CLOSURE	ZIPPER	ZIPPER	ZIPPER	ZIPPER	HOOK & LOOP	HOOK & LOOP	HOOK & LOOP	ZIPPER
REFLECTIVE ACCENTS	--	--	YES	--	--	YES	--	--
COLOR	HI-VIS LIME OR GRAY	BLUE	HI-VIS LIME	HI-VIS LIME	HI-VIS LIME	HI-VIS ORANGE OR TAN	TAN	BLACK
SIZING (CHEST CIRCUMFERENCE)	M: 36-38IN (91-97CM) L: 38-42IN (97-107CM) XL: 42-45IN (107-117CM) 2XL: 46-50IN (117-127CM) 3XL: 50-54IN (127-137CM)	M: 39IN (100CM) L: 42IN (107CM) XL: 45IN (114CM) 2XL: 48IN (122CM) 3XL: 51IN (130CM) 4XL: 54IN (137CM) 5XL: 57IN (145CM)	S: 45IN (114CM) L: 50IN (127CM) M: 55IN (140CM) XL: 60IN (152CM) 2XL: 65IN (165CM)	M: 38-41IN (97-104CM) L: 41-44IN (104-112CM) XL: 44-47IN (112-119CM) 2XL: 47-50IN (119-127CM) 3XL: 50-53IN (127-135CM) 4XL: 53-56IN (135-142CM)	S/M: 32-40IN (81-102CM) L/XL: 40-52IN (102-132CM)	S/M: 32-40IN (81-102CM) L/XL: 40-52IN (102-132CM)	S/M: 32-40IN (81-102CM) L/XL: 40-52IN (102-132CM)	S/M: 30IN (78CM) L/XL: 33IN (84CM) 2XL/3XL: 34.5IN (87CM)
CARE INSTRUCTIONS	HAND WASH & HANG DRY	MACHINE WASH & HANG DRY	HAND WASH & HANG DRY	MACHINE WASH & HANG DRY	MACHINE WASH & HANG DRY	VEST: MACHINE WASH & HANG DRY PACKS: HAND WASH	VEST: MACHINE WASH & HANG DRY PACKS: HAND WASH	VEST: MACHINE WASH & HANG DRY PACKS: HAND WASH
CUSTOM LOGO	--	YES	--	--	--	--	--	YES
⚠ PROP65	YES	YES	YES	YES	YES	YES	YES	YES

ORDER MULTIPLE: 1		
MSC #	SIZE	
68040062	M	●
79115101	L	●
79115127	XL	●
79115135	2XL	●
79115150	3XL	●
51647121	M	●
51647113	L	●
82495219	XL	●
82495243	2XL	●
91388017	3XL	●

ORDER MULTIPLE: 1		
MSC #	SIZE	
18043331	M	●
18043380	L	●
18043448	XL	●
18043455	2XL	●
09119298	3XL	●
09120437	4XL	●
01446491	5XL	●

ORDER MULTIPLE: 1		
MSC #	SIZE	
13627559	S	●
13627575	M	●
13628003	L	●
13628011	XL	●
13627583	2XL	●

ORDER MULTIPLE: 1		
MSC #	SIZE	
31826910	M	●
31826894	L	●
31827009	XL	●
31826985	2XL	●
31826977	3XL	●
38078820	4XL	●

ORDER MULTIPLE: 1		
MSC #	SIZE	
98069347	S/M	●
98069321	L/XL	●

ORDER MULTIPLE: 1		
MSC #	SIZE	
31908494	S/M	●
31826944	L/XL	●
31826969	S/M	●
31826951	L/XL	●
VEST ONLY		
MSC #	SIZE	
36114478	S/M	●
20776852	L/XL	●
36191864	S/M	●
36191955	L/XL	●
ICE PACKS ONLY		
MSC #	SIZE	
36114007	S/M	●
39245238	L/XL	●
EXTENDERS		
MSC #	SIZE	
31827074	-	●
31827066	-	●

ORDER MULTIPLE: 1		
MSC #	SIZE	
31826936	S/M	●
31826928	L/XL	●
VEST ONLY		
MSC #	SIZE	
87527552	S/M	●
41346164	L/XL	●
ICE PACKS ONLY		
MSC #	SIZE	
36114007	S/M	●
39245238	L/XL	●

ORDER MULTIPLE: 1		
MSC #	SIZE	
98069313	S/M	●
98069339	L/XL	●
VEST ONLY		
MSC #	SIZE	
98069305	S/M	●
98069354	L/XL	●
ICE PACKS ONLY		
MSC #	SIZE	
97799936	4-Pack	●

In stock and ready to ship. Order today.
800.645.7270 | mscdirect.com

Available
Today At

MSC



WHAT COOLING TECH
IS RIGHT FOR ME?