

DEWALT

PERFORMANCE REDEFINED™

DCK2101QQ2 20V MAX* XR® HAMMER DRILL/ IMPACT 2-TOOL COMBO KIT WITH XR POWERPACK™ BATTERIES

Take on a wide range of demanding applications with the 20V MAX* XR® 3-Speed Hammer Drill and Impact 2-Tool Combo Kit with POWERPACK™ Batteries. Featuring our most powerful 20V MAX* hammer drill** and a compact impact driver designed to deliver 30% more torque†, this 2-Tool Combo Kit includes (2) 20V MAX* XR POWERPACK™ batteries.



*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18 volts.


**Based on rated maximum watts out for DEWALT 20V MAX* hammer drills currently on the market.

†Rated Torque vs. DCF885 Impact Driver with Rated Torque of 1400 in-lbs

20V MAX* XR

ICDCK2101QQ2SS

20V MAX* XR® HAMMER DRILL/ IMPACT 2-TOOL COMBO KIT WITH XR POWERPACK™ BATTERIES



*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18 volts.
**Based on rated maximum watts out for DEWALT 20V MAX* hammer drills currently on the market.

DCD1007 SPECIFICATIONS

MAX POWER	1211 MWO¹ ; 1530 MWO²
MAX BPM	0-8,500 / 0-22,100 / 0-38,250
NO LOAD SPEED (DRILLING)	0-450 / 0-1,200 / 0-2000 RPM
NO LOAD SPEED (HAMMER)	0-500 / 0-1,300 / 0-2,250 RPM
TOOL HEAD LENGTH	7.6 in.
TOOL HEAD WIDTH	2.9 in.
TOOL HEIGHT (TOOL ONLY)	8.6 in.
WEIGHT (TOOL ONLY)	4.1 lbs.
CHUCK SIZE	1/2 in.

¹ 1211 MWO based on using DCB2104 battery included.

² 1530 MWO based on using DCB2108 battery (sold separately).

DCF845 SPECIFICATIONS

DRIVE SIZE	1/4 in. Quick Release Hex Shank
MAX TORQUE	1,825 in.-lbs.
NO LOAD SPEED	0-1,500 / 0-2,800 / 0-3,400 RPM
IMPACTS/MIN	0 - 4,200 IPM
WEIGHT (TOOL ONLY)	2.0 lbs.
SPEED SETTINGS	3 Speed Modes

KIT INCLUDES

DCK2101QQ2

- (1) DCD1007 20V MAX* XR® 1/2 in. 3-Speed Hammer Drill
- (1) DCF845 20V MAX* XR® 1/4 in. 3-Speed Impact Driver
- (2) DCB2104 XR POWERPACK™ 4Ah Batteries
- (1) Charger, (1) Contractor Bag
- (2) Belt Hooks and (1) Side Handle



WARRANTY

TOOL WARRANTY

3
YEAR

LIMITED WARRANTY

1
YEAR

FREE SERVICE

90
DAY

MONEY BACK GUARANTEE

BATTERY WARRANTY

3
YEAR

LIMITED WARRANTY

3
YEAR

FREE SERVICE