



Sta-Plex™ Extreme Pressure Premium Red Grease, 14 Wt Oz No. SL3190 | Item# 1007890 | Case# 1007889

Product Description

A superior multi-purpose certified lithium complex based NLGI #2 grease. Contains extreme pressure, anti-wear, & anti-oxidation additives. Ideal for high temperature & performance applications. Drop point 500°F

Applications

Ind. mining, metal production, machining, plastic molding, pumps, electric motors, ball & roller bearings, kilns, assembly plants, drying ovens, trucks, automobiles, buses, construction equipment, off-road operations, tractors, mowers, reapers, water pumps

Unit Package Description

14 Ounce Cartridge

Brand

Sta-Lube

Generic Description 1

Premium Red Grease

Net Fill

14 Wt Oz

UPC Code

072213319002

Unit Dimensions

9.31H x 2.13W x 2.13D in

Units Per Case

10

Case Dimensions

9.5H x 4.5W x 11.38D in

Cases Per Pallet

150

Case Weight

10 lbs

I 2 of 5 Code

30072213319003

Appearance

Red Semi-Solid to Solid Grease

Base Type

Lithium Complex

Flash point (F)

475°F

Flash point (C)

246°C

Flammability Class - CPSC

None

Spec Gravity Concentrate

0.9 at 60°F

NLGI Grade

2

Timken OK Load Lbs.


60 Lbs Min

Plastic Safe

Not Determined

Evaporation Rate

<1 (butyl acetate=1)



Last revised: 7/30/2019

Page 1 of 2




Chemical Solutions to Keep You Moving™

f t y o i n • 800-272-8963 • crcindustries.com

CRC Industries, Inc. is a global leader in the production of specialty chemicals for maintenance, repair and operational professionals and do-it-yourselfers serving the automotive, industrial, electrical, marine, heavy truck, hardware and aviation markets. CRC trademarked brands include: CRC®, K&W®, Sta-Lube®, SmartWasher®, Marykate®, Weld-Aid®, Ambersil®, KF®, Kontakt Chemie®, Ados®, Action Can®, and Kitten®.

©2019 CRC Industries, Inc.



Working Temp (F)	-20 to 325°F
Working Temp (C)	-27 to 162°C
4 Ball EP	77 LWI, 500 Kg Weld
4 Ball Wear	0.4 typical; 0.6 Max
Drop Point	500+ °F
Elastomer Compatibility	0 to 30% vol; 0 to 15 hard
Leakage	10g Max
Low Temp Torque	15.5 Max
Oil Separation	<5
Oxidation Stability	5
Pour Point (F)	5°F
Pour Point (C)	-15°C
ISO Viscosity Grade	230
Water Washout	<5
Worked Penetration	265 to 295
Propellant	None
NSF Category Code	H2
NSF Number	145511
DOT Proper Shipping Name	Not Regulated
VOC % (Consumer Product def)	1
VOC g/L (Consumer Product def)	9
VOC lbs/gal (Consumer Prod def)	0.075
VOC Category	Not Regulated
Removal (How To)	Remove with a degreaser or brake cleaner product.

Last revised: 7/30/2019
Page 2 of 2



Chemical Solutions to Keep You Moving™
f t y o i n • 800-272-8963 • crcindustries.com

CRC Industries, Inc. is a global leader in the production of specialty chemicals for maintenance, repair and operational professionals and do-it-yourselfers serving the automotive, industrial, electrical, marine, heavy truck, hardware and aviation markets. CRC trademarked brands include: CRC®, K&W®, Sta-Lube®, SmartWasher®, Marykate®, Weld-Aid®, Ambersil®, KF®, Kontakt Chemie®, Ados®, Action Can®, and Kitten®.

©2019 CRC Industries, Inc.