



Multi Purpose

Viral Protection



Light Duty

Antimicrobial Protection for High-Traffic Touch Points

- The only industrial glove designed with Ionic+™, an EPA-registered antimicrobial technology
- Leverages the antimicrobial power of silver to protect gloves from microbial impacts
- All day comfort with high dexterity in a light-weight breathable design
- Self-Sanitizing 360° antimicrobial protection of both the liner and coating



Industries

- Manufacturing
- Logistics
- Transportation
- Recycling and Waste Disposal
- Hospitality
- Housekeeping
- Sales
- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Utilities
- Warehousing

Applications

- Assembly line
- Packaging
- Delivery of finished equipment
- Event Management/Waitstaff
- Cleaning/Maintenance/Repair
- Drivers/Operators/Inspectors
- Shared surfaces/tools/touchscreens
- Cashiers/Clerks/Money Handling

Key Features

- The only industrial glove designed with Ionic+™, an EPA-registered antimicrobial technology - EPA Registration #70927-6
- Self-Sanitizing 360° antimicrobial protection of both the liner and coating
- Ionic+™ is permanent and lasts the life of the product
- Touchscreen compatible for use with a wide range of devices
- Compliant with EU Biocides Regulation 528/2012 for treated articles
- Designed so coating does not inhibit antimicrobial action
- Protects glove from bacterial-related odor, stain, and fabric degradation

Technologies



EPA REGISTERED
ANTIMICROBIAL



ionic+ Antimicrobial Technology



Touchscreen Compatible



ZONZ™

Comfort Fit Technology

Performance Standards & Regulatory Compliance

REACH Compliant



2131A



2131



ABR



CUT

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-100	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Conductive Fiber, Nylon, Ionic+® active antimicrobial liner Cuff Style: Knitwrist	15	6, 7, 8, 9, 10	204-274 mm 8.03-10.78 inches	Grey	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.